

GENERAL NOTES:

1. CONNECT ALL CIRCUITS TO PANEL 5R2A UNLESS NOTED OTHERWISE.
2. REFER TO DRAWING E2.10.44 AND E2.10.45 FOR 480VAC MECHANICAL EQUIPMENT FEEDER SIZES.
3. MOTORS ARE PROVIDED WITH MECHANICAL EQUIPMENT AND SHOWN FOR CLARITY ONLY.

KEYNOTES:

- ND01** SEE DRAWING E8.10.43 FOR ENLARGED PLAN OF THE ELECTRICAL ROOM.
- ND02** CONNECT ALL CIRCUITS FOR FAN POWERED HOT WATER TERMINAL UNITS TO PANEL 5R2A (TYP. 8)
- ND03** PROJECTION SCREEN RECEPTACLE, MOUNT 12" FROM CEILING.
- ND04** CONNECT 100A 480VAC, 3 PH. ELEVATOR EQUIPMENT SERVICE DISCONNECT SWITCH TO SWDCA (TYP. 2). TERMINATE AT ELEVATOR CONTROL PANEL.
- ND05** CONNECT 120VAC, 20A 1 PH. ELEVATOR CONTROL LIGHTING DISCONNECT SWITCH TO PANEL 3E5A. TERMINATE AT ELEVATOR CONTROL PANEL.
- ND06** CONNECT ALL CIRCUITS FOR UNIT HEATERS TO PANEL 5R2A.
- ND07** PROVIDE STANCHION MOUNTING FOR VFDs LOCATED AT MECHANICAL EQUIPMENT. (TYP.)

